

fumapem® FS-960-RFS

General

Membrane type: Perfluorinated cation-exchange membrane – reinforced and stabilized – thickness 60 µm, with low resistance, high mechanical stability, low dimensional swelling, and high stability in acidic environment.

Application: Fuel Cell application (H₂-PEMFC), preferably with Oxygen under enhanced pressure.

Membranes are identified by membrane type and identification number (Lot Number). Please refer to this type and identification number in case of queries.

Delivery

The membrane is the transparent foil, delivered on a backing layer (colorless rigid PET foil). Carefully separate the membrane from the backing foil or in the other way around, depending on the convenience. The membrane is ready for use.

Handling

Keep membrane package closed / sealed when unused. Unpack membrane only for direct use and process it immediately after opening. Store, handle and process the membrane in a clean and dust-free area. Use only new and sharp knives or blades, when cutting the membrane.

Always wear protective gloves when handling the membrane. Handle with care, be sure not to puncture, crease or scratch the membrane, otherwise leaks will occur. All surfaces which may get into contact with the membrane during inspection, storage, pretreatment and mounting must be free of sharp edges or angles.

Pretreatment

The membrane does not need any pretreatment and is ready for use. Please assemble the membrane in dry form.

If you have any concerns about storage, chemical stability, and pretreatment please feel free to contact us for further information.

FUMATECH BWT GmbH

Carl-Benz Strasse 4
74321 Bietigheim-Bissingen
Phone: +49-(0)-7142-3737-900
Fax: +49-(0)-7142-3737-999
Email: sales@fumatech.com

Physical and chemical data of fumapem® FS-960-RFS

fumapem®	unit	FS-960-RFS
membrane type		cation exchange membrane
appearance		transparent / light brown
backing foil		PET
reinforcement		yes
counter ion		H ⁺ form
delivery form		dry
thickness (dry)	µm	55 – 65
IEC (ion exchange capacity)	meq g ⁻¹	1.07 – 1.31
conductivity in H ₂ O at T = 25 °C in H-form ^{a)}	mS cm ⁻¹	> 50
area resistance at 80 °C and 100 % rel. humid. ^{b)}	Ω cm ²	< 0.12
area resistance at 80 °C and 50 % rel. humid. ^{b)}	Ω cm ²	< 0.2
uptake in H ₂ O at T = 25 °C in H-form ^{c)}	wt %	< 25
dimensional swelling in H ₂ O at T = 25 °C in H-form ^{d)}	%	< 15
Young's modulus at 23 °C / 50 % r.h. ^{e)}	MPa	> 380
yield strength at 23 °C / 50 % r.h. ^{e)}	MPa	> 24
tensile strength at 23 °C / 50 % r.h. ^{e)}	MPa	> 15
elongation at break at 23 °C / 50 % r.h. ^{d)}	%	> 100
Version ^{f)}	2.1	Valid from August 20 th 2020

a) measured in two-electrode cell (through-plane), sample activated in 10 % H₂SO₄, T = 80 °C, 24 hrs before measurement

b) determined from EIS during fuel cell operation

c) reference membrane dried over P₂O₅ *in vacuo*, sample activated in 10 % H₂SO₄, T = 80 °C, 24 hrs before measurement

d) reference membrane dried at ambient conditions (25 °C, 50 % r.h.), sample activated in 10 % H₂SO₄, T = 80 °C, 24 hrs before measurement

e) determined by stress-strain measurement at T = 25 °C and 50 % r.h., according to DIN EN 527-1

f) Changes without prior notices may apply.

Note: The product is not certified for drinking water applications. The data are not measured directly on the item supplied. The data sheet does not release the customer of the necessity of a goods inwards control procedure. All information included in this data sheet is based on tests and data believed to be reliable. The data do not imply any warranty or performance guarantee. It is the user's responsibility to examine performance, suitability and durability of the product for the intended purpose. FUMATECH BWT GmbH does not assume any liability for patent infringement resulting from the use of this product. Fumapem® is a trademark of company FUMATECH BWT GmbH.

Hereby, it is certified that all results of the measured item comply with the margins of the internal specification defined in the technical datasheet. All measurements and data recording are conducted in accordance with standardized procedures following the ISO 9001 certification.

FUMATECH BWT GmbH

Carl-Benz Strasse 4

74321 Bietigheim-Bissingen

Phone: +49-(0)-7142-3737-900

Fax: +49-(0)-7142-3737-999

Email: sales@fumatech.com